



### Kaubanduslik olek

Tootmine lõpetatakse: 15 detsember 2021

Teeninduse lõpp varsti: 15 detsember 2021

⚠ Võetakse tootmisest maha

### Main

Range	PratiKa
Product or component type	Socket
Device short name	PratiKa socket
Plug, socket category	Extra-low voltage
Poles description	3P
Network type	AC
Outlet standard	Industrial

### Complementary

Mounting mode	Wall-mounted
Plug, socket, control station shape	Angled
[In] rated current	16 A
[Ue] rated operational voltage	20...25 V 40...50 V
Network frequency	401/500 Hz
Secondary keyway clockwise position	11 h
Plug, socket material	Housing self-extinguishing engineering polymer
Contacts material	Pins stainless steel Sleeves nickel plated brass Springs stainless steel
Connections - terminals	Captive screws, completely loosened
Cable cross section	4...10 mm <sup>2</sup>
Cable outer diameter	6...23 mm
Cable entry	Fair lead
Thread type	Pg 21
Net weight	0,214 kg
Base dimension	70 x 82 mm
Height	118 mm
Width	70 mm
Depth	81 mm
Colour	Grey RAL 7035)
Voltage colour	Green

## Environment

Standards	EN 60309-2 EN 60309-1
IP degree of protection	IP44 IEC 60529
IK degree of protection	IK08 EN 62262
Fire resistance	850 °C IEC 60695-2-11
Relative humidity	50 % 40 °C 70 % 30 °C 90 % 20 °C
Ambient air temperature for operation	35 °C 86400 s )

## Packing Units

Osa tüüp pakil 1	PCE
Osade arv pakis 1	1
Pakk 1 kaal	200 g
Pakk 1 kõrgus	7 cm
Pakk 1 laius	7 cm
Pakk 1 pikkus	12 cm

## Contractual warranty

Garantii	18 months
----------	-----------