



Main

Range	PratiKa
Product or component type	Wander socket
Device short name	PratiKa socket
Plug, socket category	Extra-low voltage
Poles description	2P
Network type	AC
Outlet standard	Industrial

Complementary

Plug, socket, control station shape	Straight
[In] rated current	16 A
[Ue] rated operational voltage	20...25 V 40...50 V
Network frequency	401/500 Hz
Secondary keyway clockwise position	11 h
Plug, socket material	Housing self-extinguishing engineering polymer
Contacts material	Pins stainless steel Sleeves nickel plated brass Springs stainless steel
Connections - terminals	Captive screws
Cable cross section	4...10 mm ²
Cable outer diameter	6...23 mm
Cable entry	Cable gland
Thread type	Pg 21
Net weight	0,186 kg
Height	72 mm
Width	72 mm
Depth	172 mm
Colour	Grey RAL 7035)
Voltage colour	Green

Environment

Standards	IEC 60309-2 IEC 60309-1
IP degree of protection	IP44 IEC 60529
IK degree of protection	IK08 EN 62262
Fire resistance	850 °C IEC 60695-2-1
Relative humidity	50 % 40 °C 70 % 30 °C 90 % 20 °C
Ambient air temperature for operation	35 °C 86400 s) -25...40 °C

Packing Units

Osa tüüp pakil 1	PCE
Osade arv pakis 1	1
Pakk 1 kaal	170 g
Pakk 1 kõrgus	7,2 cm
Pakk 1 laius	7,2 cm
Pakk 1 pikkus	17,2 cm

Contractual warranty

Garantii	18 months
----------	-----------