

AR4018SPX432

NetShelter CX 18U Secure Soundproof Server Room in a Box Enclosure - Shock Packaging - White



Overview

Description	NetShelter CX Enclosure with integrated cooling and noise dampening is ideal for office environments. The cabinet is paired with a shock absorbing pallet, unloading ramp and impact resistant shell. The system has been engineered, tested and approved for secure shipment of fully integrated IT systems
Model Name	NetShelter CX 18U Secure Soundproof Server Room in a Box Enclosure - Shock Packaging - White
Includes	Key(s) , Pallet ramps , Reusable packaging , Unpacking sheet
Product Distribution	Afghanistan , Albania , Algeria , Andorra , Angola , Armenia , Australia , Austria , Azerbaijan , Bahrain , Bangladesh , Belarus , Belgium , Benin , Bhutan , Bosnia And Herzegovina , Botswana , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Canada , Central African Republic , Chad , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Cook Islands , Cote D'Ivoire , Croatia , Cyprus , Czech Republic , Denmark , Djibouti , East Timor , Egypt , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Guadeloupe , Guinea , French Guiana , Hungary , Iceland , India , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Madagascar , Malawi , Malaysia , Mali , Malta , Martinique , Mauritania , Mauritius , Mayotte , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , New Zealand , Niger , Nigeria , Norway , Oman , Pakistan , Papua New Guinea , Philippines , Poland , Portugal , Qatar , Reunion , Romania , Russian Federation , Rwanda , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Tunisia , Turkey , Turkmenistan , Turks And Caicos Islands , Uganda , Ukraine , United Arab Emirates , United States , Uzbekistan , Viet Nam , Western Sahara , Yemen , Zambia , Zimbabwe

Input

Nominal Input Voltage	100V , 110V , 115V , 120V , 127V , 200V , 208V , 220V , 230V , 240V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	IEC-320 C14

Physical

Net Weight	144.0 kg
Maximum Height	1015.0 mm
Maximum Width	750.0 mm
Maximum Depth	1130.0 mm
Shipping Weight	220.0 kg

Shipping Height	1280.0 mm
Shipping Width	1000.0 mm
Shipping Depth	1300.0 mm
Maximum Mounting Depth	33.94
Rack Height	18 U
Color	White
Units per Pallet	1.0

Conformance

Approvals	EIA 19 Inch , WEEE
Standard warranty	2 year (manufacturer's defect)

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs