



## Main

Range	Thalassa
Product name	Thalassa PLA
Enclosure type	Multi-purpose
Product or component type	Suitable enclosure
Version	PLAZ
Nominal height	1250 mm
Nominal width	1000 mm
Nominal depth	420 mm
Enclosure mounting	Floor-standing
Device composition	1 top part 1 bottom part 2 side part 2 door 2 rear panel 1 plinth

## Complementary

Body type	Sealed top and open bottom part assembled with side parts
Door type	Plain front
Number of doors	2
Door opening side	Right and left 120 °)
Lock type	4 points lock, handle with 5 mm double bar insert
Accessibility for operation	Rear Bottom Front
Removable parts	Door by hinges Rear panel by fixing element
Material	polyester reinforced with fibreglass
Colour	Grey (RAL 7035)

Standards	IEC 62208
Product certifications	Veritas
Electrical insulation class	Class II

### Environment

IP degree of protection	IP54 IEC 60529 plinth type open bottom)
IK degree of protection	IK10 IEC 62262 plain door)
Fire resistance	960 °C IEC 62208
Ambient air temperature for storage	-35...90 °C

### Packing Units

Osa tüüp pakil 1	PCE
Osade arv pakis 1	1
Pakk 1 kaal	63,246 kg
Pakk 1 kõrgus	141,5 cm
Pakk 1 laius	103 cm
Pakk 1 pikkus	48 cm

### Offer Sustainability

Jätksuutliku pakkumise olek	Green Premium toode
REACH-määrus	<a href="#">REACH-deklaratsioon</a>
ELi RoHS direktiiv	Ennetav vastavus (toode ei jää EL-i RoHS seadustega määratud piiridesse) <a href="#">ELi RoHS deklaratsioon</a>
Elavhõbedavaba	Jah
RoHS eranditeave	<a href="#">Jah</a>
Hiina EoHS regulatsioon	<a href="#">Hiina RoHS deklaratsioon</a> Toode ei kuulu Hiina RoHS sfääri. Ainedeklaratsioon teavitamiseks.
Keskkonnaalane avaldus	<a href="#">Toote keskkonnaprofiil</a>