



XVDLS34 pole välja vahetatud. Lisateabe saamiseks võtke ühendust klienditoega.

! Tootmisest maas

### Main

Range of product	Harmony XVD Optimum
Product or component type	Complete miniature beacon
Beacon or indicator bank unit type	Base unit with direct fixing mode Illuminated unit
Signalling type	Steady
Mounting diameter	45 mm
Component name	XVDLS
Material	Glass reinforced polyamide (base unit) Polycarbonate (illuminated unit)
Light source	Red bulb not included
Bulb type	Incandescent with BA 15d
[Us] rated supply voltage	$\leq 230$ V
Power dissipation in W	$< 5$ W

### Complementary

Connections - terminals	Screw clamp terminals, connection capacity: $\leq 1 \times 1.5$ mm <sup>2</sup> with cable end
Cable entry	1 entry tapped for Pg 7
[Ui] rated insulation voltage	250 V conforming to IEC 60947-1
[Uimp] rated impulse withstand voltage	4 kV conforming to IEC 60947-1
CAD overall width	45 mm
CAD overall height	104 mm
CAD overall depth	45 mm
Terminals description ISO n°1	(COM-1)PW (GND)GROUND
Product weight	0.08 kg

### Environment

Product certifications	CSA UL
Standards	EN/IEC 60947-5-1
Protective treatment	TC
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C

---

Electrical shock protection class	Class II conforming to IEC 60536
IP degree of protection	IP40 conforming to IEC 60529

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---