


Product datasheet

Specifications



LINERGY LGYE PROFILE 800A FOR A VERTICAL INSTALLATION LENGTH 1670MM

04503

! Discontinued

! Discontinued on: Jan 18, 2022

Main

Range	Linery
Range Of Product	Linery
Product Or Component Type	Profile busbar
Product Name	Linery LGY
Range Compatibility	Prisma Prisma P enclosure
Busbar Description	Linery
Quantity Per Set	Set of 1

Complementary

Installation Direction	Vertical, operating position: rear Vertical, operating position: lateral
Installation Description	Cubicle - width 650 mm Cubicle - width 650 + 150 mm
[Ui] Rated Insulation Voltage	1000 V
[Uimp] Rated Impulse Withstand Voltage	12 kV (degree of pollution: 3)
[Ie] Rated Operational Current	800 A
[Icw] Rated Short-Time Withstand Current	25 kA (1 s) for 3 supports (rear position) 30 kA (1 s) for 3 supports (lateral position) 30 kA (1 s) for 4 supports (rear position)
Permissible Current	840 A at 35 °C: <= IP31 760 A at 35 °C: > IP31
Busbar Cross Section	32.5 x 42.5 mm
Length	1670 mm
Net Weight	1.64 kg
Type Of Busbar Connection	Single t-slot
Connection Pitch	Free connection position

Environment

Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 أشهر
----------	---------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information