Product datasheet

Specification





Kaedra - for power outlet - 2 openings - 1 x 5 modules

13178

Main

Range	Mureva
Product Name	Mureva Enclosure
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Enclosure for power outlet
Mounting Plate Description	Without mounting plate

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	10
Number Of 18 Mm Modules Per Row	5
Total Number Of 18 Mm Modules	5
Number Of Horizontal Rows	1
Electrical Insulation Class	Class II Double insulation
Number Of Openings Of Interface	2
Number Of Plates	1 for push-button controls 2 for 65 x 85 power outlets
Provided Equipment	1 plate for push-button control 2 plate for 65 x 85 power outlet
Type Of Front Cover	Transparent
Power Dissipation In W	12 W
[In] Rated Current	63 A
Type Of Rail	DIN
Number Of Pre-Cutouts Pg Iso	3
Locking Options Description	Optional keylock
Enclosure Material	Housing: self-extinguishing polymer
Net Weight	1.4 kg
Base Dimension	90 x 100 mm
Width	138 mm
Height	460 mm
Depth	160 mm
Internal Depth	91 mm

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Colour Door: transparent green
Enclosure: light grey (RAL 7035)

Environment

Standards	IEC 60670 IEC 61439-3 EN 50262 EN 62262 IEC 60695-2-1	
Fire Resistance	650 °C conforming to IEC 60695-2-1	
Ip Degree Of Protection	IP65 conforming to IEC 60529	
Ik Degree Of Protection	IK09 conforming to EN 50102	
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013	
Overvoltage Category	II	
Ambient Air Temperature For Operation	-2540 °C	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	47.000 cm
Package 1 Width	16.000 cm
Package 1 Length	17.000 cm
Package 1 Weight	1.416 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	66
Package 2 Height	80.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	105.456 kg

Contractual warranty

Warranty	18 months	
----------	-----------	--

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >







Lower Impact Materials Transparency RoHS/REACh

Resource performance



Minimum Percentage Of Recycled Plastic Content

Well-being performance



Rohs Exemption Information



Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	No need of specific recycling operations	