

Product datasheet

Specifications



Mini Pragma surface enclosure - IP 40 - 1 x 18 modules - transparent door

13350

⚠ Discontinued on: Nov 1, 2020

⚠ Discontinued

Main

Range	Mini Pragma
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	18
Nb Of Horizontal Rows	1
Provided Equipment	1 marking kit 1 insulating plug
Type Of Door	Transparent

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	36
Total Number Of 18 Mm Modules	18
[In] Rated Current	63 A
Type Of Rail	DIN
Locking Options Description	Keylock option
Enclosure Material	Enclosure: self-extinguishing material
Colour	Enclosure: white (RAL 9003)

Environment

Standards	EN 60439-3 IEC 23-3 EN 50102 IEC 60695-2-1 IEC 60529 IEC 60439-3
Fire Resistance	Back part: 650 °C (30 s) conforming to IEC 60695-2-1 Front face: 650 °C (30 s) conforming to IEC 60695-2-1
Ik Degree Of Protection	IK07 conforming to EN 50102

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	22 cm
Package 1 Length	36.5 cm
Package 1 Weight	0.84 kg

Contractual warranty

Warranty	18 months
----------	-----------