

Product datasheet

Specifications



Acti 9 Vertical TPN 18way with 3P isolator 125A incomer provision

A9HV318XI125

Main

Range	Acti 9 Disbo
Product name	Acti9 Vertical TPN
Product or component type	Distribution board
Device application	Low voltage electrical distribution
Enclosure type	Standard
Door type	Flat
Provided equipment	enclosure pan assembly earth terminal block neutral terminal block
Colour	White (RAL 9003)

Complementary

[Ie] rated operational current	125 A
[Icw] rated short-time withstand current	17 kA for 0.25 s
[Ipk] rated peak withstand current	34 kA
Enclosure mounting	Flush
Incomer device	3P isolator
Number of ways	18 ways
Enclosure material	Powder coated sheet steel
Height	555 mm
Width	425 mm
Depth	125 mm
IP degree of protection	IP41
Targeted country	Egypt

Environment

Standards	IEC 61439-3
Ambient air temperature for operation	-5...50 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	10.4 kg
Package 1 Height	11.7 cm
Package 1 width	42.5 cm
Package 1 Length	55.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile