

Product datasheet

Specifications



Acti 9 Vertical TPN 42way with 3P NSX 250A incomer provision

A9HV342XNSX250

Main

| | |
|---------------------------|---|
| Range | Acti9 Disbo |
| Product name | Acti9 Vertical TPN |
| Product or component type | Distribution board |
| Device application | Low voltage electrical distribution |
| Enclosure type | Standard |
| Door type | Flat |
| Provided equipment | enclosure pan assembly earth terminal block neutral terminal block |
| Colour | White (RAL 9003) |

Complementary

| | |
|--|---------------------------|
| [Ie] rated operational current | 250 A |
| [Icw] rated short-time withstand current | 25 kA for 0.3 s |
| [Ipk] rated peak withstand current | 52.5 kA |
| Enclosure mounting | Flush |
| Incomer device | 3P MCCB |
| Number of ways | 42 ways |
| Enclosure material | Powder coated sheet steel |
| Height | 975 mm |
| Width | 425 mm |
| Depth | 148 mm |
| IP degree of protection | IP41 |
| Targeted country | Egypt |

Environment

| | |
|---------------------------------------|-------------|
| Standards | IEC 61439-3 |
| Ambient air temperature for operation | -5...50 °C |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 14.0 cm |
| Package 1 Width | 42.5 cm |
| Package 1 Length | 87.5 cm |
| Package 1 Weight | 17.1 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |

Recommended replacement(s)