

Product datasheet

Specifications



Miniature circuit-breaker, Acti9 iK60N, 1P, 40 A, C curve, 6000 A (IEC 60898-1)

A9K24140

Main

Device application	Distribution
Range	Acti 9
Product name	Acti9 iK60
Product or component type	Miniature circuit-breaker
Device short name	IK60N
Poles description	1P
Number of protected poles	1
[In] rated current	40 A at 30 °C
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	6000 A Icn at 230 V AC 50/60 Hz conforming to EN/IEC 60898-1
Suitability for isolation	Yes conforming to EN/IEC 60898-1
Standards	EN/IEC 60898-1
Product certifications	SNI

Complementary

Network frequency	50/60 Hz
Magnetic tripping limit	5...10 x In
[Ics] rated service breaking capacity	6000 A 100 % conforming to EN/IEC 60898-1 - 230 V AC 50/60 Hz
Limitation class	3 conforming to EN/IEC 60898-1
[Ui] rated insulation voltage	440 V AC 50/60 Hz conforming to EN/IEC 60898-1
[Uimp] rated impulse withstand voltage	4 kV conforming to EN/IEC 60898-1
Contact position indicator	No
Control type	Toggle
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail

9 mm pitches	2
Height	85 mm
Width	18 mm
Depth	78.5 mm
Net weight	100 g
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Locking options description	Padlocking device
Connections - terminals	Tunnel type terminal (top or bottom) 1...35 mm ² rigid Tunnel type terminal (top or bottom) 1...25 mm ² flexible
Wire stripping length	14 mm for top or bottom connection
Tightening torque	3.5 N.m top or bottom
Earth-leakage protection	Without

Environment

IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	2 conforming to EN/IEC 60898-1
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	120.0 g
Package 1 Height	1.8 cm
Package 1 width	7.5 cm
Package 1 Length	9.4 cm
Unit Type of Package 2	P12
Number of Units in Package 2	1056
Package 2 Weight	147.72 kg
Package 2 Height	50 cm
Package 2 width	80 cm
Package 2 Length	120 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	12
Package 3 Weight	1.498 kg
Package 3 Height	8.6 cm
Package 3 width	9.6 cm
Package 3 Length	21.8 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------