

# Product datasheet

Specifications



## Miniature circuit-breaker, Acti9 iK60N, 2P, 20 A, C curve, 6000 A (IEC 60898-1)

A9K24220

### Main

Device application	Distribution
Range	Acti 9
Product name	Acti9 iK60
Product or component type	Miniature circuit-breaker
Device short name	IK60N
Poles description	2P
Number of protected poles	2
[In] rated current	20 A at 30 °C
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	6000 A Icn at 230 V AC 50/60 Hz conforming to EN/IEC 60898-1
Suitability for isolation	Yes conforming to EN/IEC 60898-1
Standards	EN/IEC 60898-1

### Complementary

Network frequency	50/60 Hz
Magnetic tripping limit	5...10 x In
[Ics] rated service breaking capacity	6000 A 100 % conforming to EN/IEC 60898-1 - 230 V AC 50/60 Hz
Limitation class	3 conforming to EN/IEC 60898-1
[Ui] rated insulation voltage	440 V AC 50/60 Hz conforming to EN/IEC 60898-1
[Uimp] rated impulse withstand voltage	4 kV conforming to EN/IEC 60898-1
Contact position indicator	No
Control type	Toggle
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	4

Height	85 mm
Width	36 mm
Depth	78.5 mm
Net weight	200 g
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Locking options description	Padlocking device
Connections - terminals	Tunnel type terminal (top or bottom) 1...25 mm <sup>2</sup> rigid Tunnel type terminal (top or bottom) 1...16 mm <sup>2</sup> flexible
Wire stripping length	14 mm for top or bottom connection
Tightening torque	2 N.m top or bottom
Earth-leakage protection	Without

## Environment

IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	2 conforming to EN/IEC 60898-1
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	195 g
Package 1 Height	3.5 cm
Package 1 width	7.5 cm
Package 1 Length	9.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Weight	1.225 kg
Package 2 Height	8.5 cm
Package 2 width	10 cm
Package 2 Length	22 cm
Unit Type of Package 3	S03
Number of Units in Package 3	66
Package 3 Weight	13.897 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>REACH free of SVHC</b>	Yes
<b>EU RoHS Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>
<b>Toxic heavy metal free</b>	Yes
<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>
<b>WEEE</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
<b>Contractual warranty</b>	
<b>Warranty</b>	18 months