Product datasheet

Specification





switch disconnector iSW - 2P - 125 A - 415 V

A9S65292

Main

Range	Acti9	
Product Name	Acti9 iSW	
Product Or Component Type	Switch disconnector	
Device Short Name	iSW	
Device Application	Control Isolation	
Poles Description	2P	
Utilisation Category	AC-22A	
Suitability For Isolation	Yes	

Complementary

[le] Rated Operational Current	125 A at 415 V AC 50/60 Hz
[Ue] Rated Operational Voltage	415 V AC 50/60 Hz
[Icm] Rated Short-Circuit Making Capacity	5 kA switch-disconnector alone
[Icw] Rated Short-Time Withstand Current	1500 A
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	6 kV
Control Type	Toggle
Local Signalling	ON/OFF indication
Contact Position Indicator	Yes
Mounting Mode	Fixed
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	Top or bottom: YES
9 Mm Pitches	4
Height	85 mm
Width	36 mm
Depth	73 mm
Colour	White
Mechanical Durability	20000 cycles
Electrical Durability	2500 cycles

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Connections - Terminals	Tunnel type terminals (top or bottom) - <= 1 x 50 mm² - rigid Tunnel type terminals (top or bottom) - <= 1 x 35 mm² - flexible Tunnel type terminals (top or bottom) - <= 1 x 35 mm² - flexible with ferrule
Wire Stripping Length	14 mm
Tightening Torque	3.5 N.m

Environment

Standards	IEC 60947-3 EN 60947-3
Ip Degree Of Protection	IP20
Pollution Degree	3
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-2560 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	7.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	167.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	8.5 cm
Package 2 Width	10.0 cm
Package 2 Length	22.0 cm
Package 2 Weight	1.07 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	66
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	12.257 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
②	Rohs Exemption Information Yes
Ø	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations