



Main

Range	Actassi
Product	Patch cord
Colour	Grey
Cable shielding type	UTP

Complementary

Type of cable	4 pair cables
Rated voltage	150 V AC
[In] rated current	1.5 A
Insulation resistance	500 MOhm
Cable length (customisable value in configurator)	0...1 m
Communication network category	6
Contacts material	Phosphor bronze with 50 micro-inches gold over 100 micro-inches nickel
Contact resistance	10 mOhm
AWG	AWG 24
Attenuation	Guaranteed: 0.1 dB
Far end crosstalk [FEXT]	49.8 dB
Power sum far end crosstalk [PSFEXT]	46.9 dB
Minimum number of matings	1000 cycles
Targeted region	Asia Pacific.

Environment

Flame retardance	CM
Standards	IEC 60603-7 FCC part 68 subpart F

Packing Units

Package 1 Weight	41.700 g
Package 1 Height	0.200 mm
Package 1 width	210.000 mm
Package 1 Length	302.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins