

Product datasheet

Specifications



Actassi - patch panel - category 6 - UTP - 24 Port - 1U - straight unloaded



ACTPPS24NSU_E

! Discontinued on: 04 December 2022

! To be end-of-service on: 03 April 2023

! To be discontinued

Main

Range of product	Actassi
Product or component type	Patch panel
Device presentation	Empty
Provided equipment	Without RJ45 connectors

Complementary

[In] rated current	1.5 A
Number of port	24 port of UTP
Product compatibility	standard 19" cabinet/rack
Communication network category	6 5e
Contact resistance	20 μ Ohm
Insulation resistance	\geq 10 MOhm
Minimum number of matings	750 cycles
Number of rack unit	1U
Type of connector	S-110 keystone

Environment

Ambient air temperature for operation	-10...50 °C
Ambient air temperature for storage	-20...60 °C
Relative humidity	0...93 %
Standards	ANSI/TIA-568-C.2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7 cm
Package 1 Width	13 cm

Package 1 Length	42 cm
Package 1 Weight	570 g
Unit Type of Package 2	S04
Number of Units in Package 2	10
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	7050 g
Unit Type of Package 3	P12
Number of Units in Package 3	80
Package 3 Height	150 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	66400 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Recommended replacement(s)