

Product datasheet

Specifications



heavy duty PowerLogic PFC Capacitor, 15/18 kvar - 440 V - 50/60Hz

BLRCH150A180B44

Main

Range of product	PowerLogic
Product or component type	Heavy duty capacitor
Network frequency	50/60 Hz
Series name	HDuty
Network harmonic content	$\leq 20\%$
Electrical parameters	15 kvar 440 V 50 Hz 18 kvar 440 V 60 Hz
Maximum permissible voltage	$1.1 \times U_n$ (8 hours over 24 hours)
Continuous overcurrent capacity	$1.8 \times I_n$
Rated voltage	440 V AC 50/60 Hz

Complementary

Dielectric losses	< 0.2 W/kvar
Power losses	< 0.5 W/kVAr
Capacitance tolerance	- 5 % to 10 %
Voltage test	$2.15 \times U_n$ AC between terminals for 10 s ≤ 660 V - 3 kV AC between terminal and container for 10 s ≥ 660 V - 6 kV AC between terminal and container for 10 s
Inrush current	$250 \times I_n$
Maximum switching operation per year	7000
Service life in hours	130000 h
Dielectric material	Metallized polypropylene film with Zn/Al alloy, special resistivity & profile, special edge (wave cut)
Impregnation material	Non-PCB dry PUR resin Biodegradable
Type of installation	Indoor installation
Connections - terminals	ClampTite terminal
Mounting mode	Upright/horizontal
Diameter	90 mm
Height	242 mm
Net weight	1.6 kg

Environment

Standards	IEC 60831-2 IEC 60831-1
IP degree of protection	IP20
Operating altitude	2000 m
Temperature class	D
Ambient air temperature for operation	-25...55 °C
Relative humidity	95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	28.5 cm
Package 1 Width	11 cm
Package 1 Length	11.8 cm
Package 1 Weight	1.7 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	2
Package 2 Height	29 cm
Package 2 Width	29 cm
Package 2 Length	39 cm
Package 2 Weight	7.5 kg
Unit Type of Package 3	S03
Number of Units in Package 3	6
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	12.6 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty 18 months

Recommended replacement(s)