

# Product datasheet

Specifications



## heavy duty PowerLogic PFC Capacitor, 25/30 kvar - 690 V - 50/60Hz

BLRCH250A300B69

### Main

Range of product	PowerLogic
Product or component type	Heavy duty capacitor
Network frequency	50/60 Hz
Series name	HDuty
Network harmonic content	$\leq 20\%$
Electrical parameters	25 kvar 690 V 50 Hz 30 kvar 690 V 60 Hz
Maximum permissible voltage	$1.1 \times U_n$ (8 hours over 24 hours)
Continuous overcurrent capacity	$1.8 \times I_n$
Rated voltage	690 V AC 50/60 Hz

### Complementary

Dielectric losses	$< 0.2 \text{ W/kvar}$
Power losses	$< 0.5 \text{ W/kVAr}$
Capacitance tolerance	- 5 % to 10 %
Voltage test	$2.15 \times U_n$ AC between terminals for 10 s $\leq 660 \text{ V} - 3 \text{ kV}$ AC between terminal and container for 10 s $\geq 660 \text{ V} - 6 \text{ kV}$ AC between terminal and container for 10 s
Inrush current	$250 \times I_n$
Maximum switching operation per year	7000
Service life in hours	130000 h
Dielectric material	Metallized polypropylene film with Zn/Al alloy, special resistivity & profile, special edge (wave cut)
Impregnation material	Non-PCB dry PUR resin Biodegradable
Type of installation	Indoor installation
Connections - terminals	ClampTite terminal
Mounting mode	Upright/horizontal
Diameter	136 mm
Height	242 mm
Net weight	3.2 kg

## Environment

Standards	IEC 60831-1 IEC 60831-2
IP degree of protection	IP20
Operating altitude	2000 m
Temperature class	D
Ambient air temperature for operation	-25...55 °C
Relative humidity	95 %

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	19 cm
Package 1 Width	19.5 cm
Package 1 Length	31 cm
Package 1 Weight	3.823 kg
Unit Type of Package 2	S06
Number of Units in Package 2	15
Package 2 Height	74 cm
Package 2 Width	60 cm
Package 2 Length	80 cm
Package 2 Weight	57.345 kg
Unit Type of Package 3	S06
Number of Units in Package 3	15
Package 3 Height	74 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	57.345 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

# Contractual warranty

---

Warranty 18 months

Recommended replacement(s)