

# Product datasheet

Specifications



## VarPlus Can HDuty Capacitor - 30/36 kvar - 400 V - 50/60Hz

BLRCH300A360B40

### Main

Range of product	PowerLogic
Product or component type	Heavy duty capacitor
Network frequency	50/60 Hz
Series name	HDuty
Network harmonic content	$\leq 20\%$
Electrical parameters	27.1 kvar 380 V 50 Hz 32.5 kvar 380 V 60 Hz 30 kvar 400 V 50 Hz 36 kvar 400 V 60 Hz 32.3 kvar 415 V 50 Hz 38.8 kvar 415 V 60 Hz
Maximum permissible voltage	$1.1 \times U_n$ (8 hours over 24 hours)
Continuous overcurrent capacity	$1.8 \times I_n$
Rated voltage	380...415 V AC 50/60 Hz

### Complementary

Dielectric losses	$< 0.2$ W/kvar
Power losses	$< 0.5$ W/kVAr
Capacitance tolerance	- 5 % to 10 %
Voltage test	$2.15 \times U_n$ AC between terminals for 10 s $\leq 660$ V - 3 kV AC between terminal and container for 10 s $\geq 660$ V - 6 kV AC between terminal and container for 10 s
Inrush current	$250 \times I_n$
Maximum switching operation per year	7000
Service life in hours	130000 h
Dielectric material	Metallized polypropylene film with Zn/Al alloy, special resistivity & profile, special edge (wave cut)
Impregnation material	Non-PCB dry PUR resin Biodegradable
Type of installation	Indoor installation
Connections - terminals	ClampTite terminal
Mounting mode	Upright/horizontal
Diameter	136 mm

Height	242 mm
Net weight	3.2 kg

## Environment

Standards	IEC 60831-2 IEC 60831-1
IP degree of protection	IP20
Operating altitude	2000 m
Temperature class	D
Ambient air temperature for operation	-25...55 °C
Relative humidity	95 %

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20 cm
Package 1 Width	19.7 cm
Package 1 Length	31.5 cm
Package 1 Weight	3.802 kg
Unit Type of Package 2	S06
Number of Units in Package 2	15
Package 2 Height	74 cm
Package 2 Width	60 cm
Package 2 Length	80 cm
Package 2 Weight	57.03 kg
Unit Type of Package 3	S06
Number of Units in Package 3	15
Package 3 Height	74 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	57.03 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

# Contractual warranty

---

Warranty 18 months

Recommended replacement(s)