

Product datasheet

Specifications



SE Easy UPS, 1000VA, Floor/Wall Mount, 230V, 4x CEE 7/3 Schuko outlets, AVR

BVS1000I-GR

Overview

Lead Time Usually in Stock

Main

Product Or Component Type	Uninterruptible power supply (UPS)
Battery Type	Lead-acid battery
Topology	Line interactive
Quantity Per Set	Set of 1
Reset	Automatic reset
Range Of Product	Easy UPS 1Ph BVS Series

Complementary

Type Of Installation	Indoor
Surge Energy	156 J
Type Of Signal	Stepped approximation to a sinewave
Protection Device Type	Surge protection device (SPD) Miniature circuit breaker (MCB) Fuse
Input Voltage	230 V AC
Output Voltage	230 V
Ip Degree Of Protection	IP20
Transfer Time	6 ms typical : 10 ms maximum
Network Frequency	45...65 Hz
Power Range	1000 VA 600 W
Electrical Connection	Input: 1 inlet Schuko CEE 7/P Output: 4 outlet Schuko CEE 7
Local Signalling	Alarm, distinctive for low battery Alarm, continuous or intermittent tone for overload LED for battery status
Number Of Batteries	1
Charging Time	8 h
Battery Voltage	12 V
Battery Capacity	9.0 Ah
Battery Life	5 year(s)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Net Weight	5.7 kg
Height	92.5 mm
Width	160.5 mm
Depth	305 mm

Environment

Relative Humidity	0...90 %, non-condensing
Operating Altitude	0...6561 ft
Ambient Air Temperature For Operation	0...40 °C
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Product Certifications	CE

Physical

Mounting Support	Wall Floor
-------------------------	---------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.200 cm
Package 1 Width	16.500 cm
Package 1 Length	30.500 cm
Package 1 Weight	5.702 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	4
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	23.458 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	32
Package 3 Height	90.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	199.664 kg
Sccl4	10731304338403

Contractual warranty

Warranty	2 years
-----------------	---------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile [End of Life Information](#)