# **Product datasheet**

Specification





# ARGUS standard outdoor 120° - blister

CCTR1P004

#### Main

| Range Of Product          | ARGUS standard movement detector                             |  |
|---------------------------|--|--|
| Range                     | ARGUS  |  |
| Product Or Component Type | Movement detector  |  |
| Load Type                 | Incandescent lamp: 1000 W, AC                                |  |
|                           | Low voltage halogen lamp with wire-wound transformer: 500 VA |  |
|                           | Low voltage halogen lamp with electronic transformer: 250 VA |  |
|                           | Fluorescent tube: 200 VA, AC                                 |  |
|                           | Compact fluorescent lamp: 3 x 23 W, AC                       |  |
|                           | Capacitive: : 6 A, 21 µF, AC                                 |  |
|                           | Capacitive: : 10 A, 14 µF, AC                                |  |
|                           | Halogen lamp: 900 W, AC                                      |  |
| Colour Tint               | White  |  |
| Type Of Packing           | Blister  |  |

## Complementary

| [Ue] Rated Operational Voltage | 220240 V  |  |
|--------------------------------|---|--|
| Network Frequency              | 50 Hz   |  |
| [Ue] Rated Operational Voltage | 220240 V  |  |
| Number Output Current          | 10 A  |  |
| Type Of Setting                | Light sensitivity adjustable<br>Time adjustment |  |
| Time Delay                     | 3 s30 min                                       |  |
| Light Intensity Adjustment     | 52000 lux                                       |  |
| Horizontal Detection Angle     | 0120 °  |  |
| Detection Range                | Frontal: 12 m                                   |  |
| Material                       | PC (polycarbonate) matt                         |  |
| Device Mounting                | Surface   |  |
| Mounting Height                | 2.5 m   |  |

#### **Environment**

| Ip Degree Of Protection               | IP55     |
|---------------------------------------|----------|
| Ambient Air Temperature For Operation | -1540 °C |

## **Packing Units**

| Unit Type Of Package 1       | PCE |
|------------------------------|-----|
| Number Of Units In Package 1 | 1   |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Package 1 Height             | 8.3 cm   |
|------------------------------|----------|
| Package 1 Width              | 18.5 cm  |
| Package 1 Length             | 27.7 cm  |
| Package 1 Weight             | 346.0 g  |
| Unit Type Of Package 2       | S04      |
| Number Of Units In Package 2 | 10       |
| Package 2 Height             | 30.0 cm  |
| Package 2 Width              | 40.0 cm  |
| Package 2 Length             | 60.0 cm  |
| Package 2 Weight             | 3.947 kg |

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

| <b>Ø</b> | Reach Free Of Svhc         |     |
|----------|----------------------------|-----|
| <b>②</b> | Toxic Heavy Metal Free     |     |
| <b>Ø</b> | Mercury Free               |     |
| <b>⊘</b> | Rohs Exemption Information | Yes |

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Compliant EU RoHS Declaration   |
| China Rohs Regulation    | China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)                                   |
| Environmental Disclosure | Product Environmental Profile   |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | End of Life Information   |