Product datasheet

Specifications



Linergy FT - Comb busbar - 63 A - 4 tap-offs - 45 mm pitch



GV2G445

Main

Range	Linergy	
Product Name	FT	
Device Short Name	GV2G	
Product Or Component Type	Comb busbar	
Accessory / Separate Part Category	Connection accessory	
Poles Description	3P	
Range Compatibility	TeSys Deca TeSys GV2 TeSys K TeSys U	
Number Of Tap-Offs	4	
[Ith] Conventional Free Air Thermal Current	63 A	
Connection Pitch	45 mm	

Complementary

Mounting Location	On terminal
[Ui] Rated Insulation Voltage	690 V
Length	179 mm
Net Weight	0.077 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	3.500 cm
Package 1 Length	18.000 cm
Package 1 Weight	78.000 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	60
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.930 kg

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 3	P06
Number Of Units In Package 3	1920
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	165.460 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc


Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes


Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	End of Life Information	

Dimensions Drawings

Sets of Busbars GV2G445, GV2G454, GV2G472, with Terminal Block GV2G05





	1	р
GV2G445 (4 x 45 mm)	179	45
GV2G454 (4 x 54 mm)	206	54
GV2G472 (4 x 72 mm)	260	72

Number of tap-offs	а			
	5	6	7	8
GV2G445	224	269	314	359
GV2G454	260	314	368	422
GV2G472	332	404	476	548