

# Product datasheet

Specifications



## Galaxy VS Parallel Maintenance Bypass Panel for 2 UPSs, 10-30kW 400V Wallmount

GVSBPAR10K30H

### Overview

Presentation	Maintenance bypass panel for complete isolation of two UPSs in parallel during service operations.
Lead Time	Usually Ships within 2 Weeks

### Physical

Height	70 cm
Width	65 cm
Depth	21 cm
Net Weight	35 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

### Environmental

Ambient Air Temperature For Operation	0...40 °C
Ambient Air Temperature For Storage	-25...55 °C

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	50 cm
Package 1 Width	80 cm
Package 1 Length	120 cm
Package 1 Weight	56 kg

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

---