Product datasheet

Specifications





Maintenance Bypass Panel, single unit, 20-60kW 400V wallmount, for Galaxy VS and Easy UPS 3S

GVSBPSU20K60H

Overview

Presentation	Maintenance bypass panel for complete isolation of the UPS during service operations.
Lead Time	Usually Ships within 2 Weeks

Physical

Height	60 cm	
Width	55 cm	
Depth	22 cm	
Net Weight	25 kg	

Environmental

Ambient Air Temperature For Operation	040 °C
Ambient Air Temperature For	-2555 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	46.000 cm
Package 1 Width	73.000 cm
Package 1 Length	80.000 cm
Package 1 Weight	43.000 kg

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >









Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Mercury Free

Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

China RohS declaration

Environmental Disclosure

Product Environmental Profile

Circularity Profile

End of Life Information