# **Product datasheet**

Specifications





# Mureva lights, Floodlight 20W 6500K, IP65 230V

IMT47209

#### Main

| Range                     | Mureva   |
|---------------------------|--|
| Range Of Product          | Mureva lights  |
| Product Or Component Type | Floodlight   |
| Device Application        | Ware-houses and parking garages<br>Residential<br>Media device support<br>Public areas<br>Secure lighting<br>Stadiums and arenas |

#### Complementary

| Type Of Installation           | Outdoor            |
|--------------------------------|--------------------|
| Total System Power             | 20 W               |
| Light Source                   | LED                |
| [Ue] Rated Operational Voltage | 230 V AC           |
| Power Factor                   | 0.7                |
| Colour Rendering Index         | R <sub>a</sub> =80 |
| Luminous Flux                  | 2000 lm            |
| Bulb Lifespan                  | 50000 h            |
| Colour Temperature             | 6500 K             |
| Colour Tint                    | Black              |
| Electrical Insulation Class    | Class F            |
| Beam Angle                     | 110 °              |
| Shape                          | Rectangular        |
| Height                         | 163.4 mm           |
| Width                          | 121.4 mm           |
| Depth                          | 26.0 mm            |
| Net Weight                     | 530 g              |

#### Environment

| Environmental Characteristic             | Weatherproof |
|--|--------------|
| Ip Degree Of Protection                  | IP65         |
| Ik Degree Of Protection                  | IK05         |
| Ambient Air Temperature For<br>Operation | -3045 °C     |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

# **Packing Units**

| U                            |            |
|------------------------------|------------|
| Unit Type Of Package 1       | PCE        |
| Number Of Units In Package 1 | 1          |
| Package 1 Height             | 17.2 cm    |
| Package 1 Width              | 17.2 cm    |
| Package 1 Length             | 17.2 cm    |
| Package 1 Weight             | 560 g      |
| Unit Type Of Package 2       | S03        |
| Number Of Units In Package 2 | 20         |
| Package 2 Height             | 30 cm      |
| Package 2 Width              | 30 cm      |
| Package 2 Length             | 40 cm      |
| Package 2 Weight             | 11.641 kg  |
| Unit Type Of Package 3       | P12        |
| Number Of Units In Package 3 | 320        |
| Package 3 Height             | 75 cm      |
| Package 3 Width              | 80 cm      |
| Package 3 Length             | 120 cm     |
| Package 3 Weight             | 198.256 kg |
|                              |            |

### **Contractual warranty**

Warranty

3 years

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Sustainable Packaging Transparency RoHS/REACh

#### **Resource performance**

Sustainable Packaging

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Compliant with Exemptions   |
| China Rohs Regulation    | China RoHS declaration<br>Product out of China RoHS scope. Substance declaration for your information                       |
| Environmental Disclosure | Product Environmental Profile   |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | End of Life Information   |