

# Product datasheet

Specifications



## Mureva lights, Floodlight 50W 6500K, IP65 230V

IMT47213

### Main

Range	Mureva
Range of product	Mureva lights
Product name	Floodlight
Product or component type	Lamp
Device application	Ware-houses and parking garages Residential Media device support Public areas Secure lighting Stadiums and arenas

### Complementary

Type of installation	Outdoor
Total system power	50 W
Light source	LED
[Ue] rated operational voltage	230 V AC
Power factor	0.9
Colour rendering index	Ra=80
Luminous flux	5000 lm
Bulb lifespan	50000 h
Colour temperature	6500 K
Colour tint	Black
Electrical insulation class	Class F
Beam angle	110 °
Shape	Rectangular
Height	215.4 mm
Width	161.4 mm
Depth	31.0 mm
Net weight	1.02 kg

### Environment

Environmental characteristic	Weatherproof
------------------------------	--------------

IP degree of protection	IP65
IK degree of protection	IK05
Ambient air temperature for operation	-30...45 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.15 kg
Package 1 Height	4.8 cm
Package 1 width	17 cm
Package 1 Length	22.5 cm
Unit Type of Package 2	S03
Number of Units in Package 2	10
Package 2 Weight	11.941 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	P12
Number of Units in Package 3	160
Package 3 Weight	203.056 kg
Package 3 Height	80 cm
Package 3 width	80 cm
Package 3 Length	120 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	3 years
----------	---------