

Product datasheet

Specifications



Mureva lights, Floodlight 150W, IP65 230V

IMT47222

Main

Range	Mureva
Range of product	Mureva lights
Product or component type	Floodlight
Device application	Ware-houses and parking garages Residential Media device support Public areas Secure lighting Stadiums and arenas

Complementary

Type of installation	Outdoor
Total system power	150 W
Light source	LED
[Ue] rated operational voltage	230 V AC
Power factor	0.9
Colour rendering index	Ra=80
Luminous flux	18000 lm
Bulb lifespan	50000 h
Colour temperature	6500 K
Colour tint	Black
Provided equipment	Sensor
Electrical insulation class	Class E
Beam angle	110 °
Shape	Rectangular
Height	342.0 mm
Width	278.0 mm
Depth	61.0 mm
Net weight	4.05 kg

Environment

Environmental characteristic	Weatherproof
------------------------------	--------------

IP degree of protection	IP65
IK degree of protection	IK06
Ambient air temperature for operation	-30...45 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11 cm
Package 1 Width	32.4 cm
Package 1 Length	40 cm
Package 1 Weight	4.542 kg
Unit Type of Package 2	S04
Number of Units in Package 2	2
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	10.518 kg
Unit Type of Package 3	P12
Number of Units in Package 3	16
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	96.144 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	5 years
----------	---------

Recommended replacement(s)