

Product datasheet

Specifications



Easy Styl - 1 module Euro-US Socket Outlet - Black

LMR5510003

Main

Range of product	Easy Styl
Range	Easy Styl
Product or component type	Socket-outlet
Number of power socket outlets	1
Device presentation	Mechanism
Range compatibility	Easy Styl
Outlet poles configuration	2P
Outlet standard	Euroamerican
Outlet standard description	Without earthing contact
Number of modules	1 module
Colour tint	Black
Type of packing	Flow-pack
Rated current	10 A at 230/250 V AC 50 Hz
Connections - terminals	screw-clamp terminals
Material	ABS + PC
Height	51 mm
Width	22 mm
Depth	45 mm
Net weight	0.021 kg
IK degree of protection	IK01
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	19.0 g
Package 1 Height	2 cm
Package 1 width	3 cm
Package 1 Length	5 cm

Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Weight	426.0 g
Package 2 Height	5.5 cm
Package 2 width	12 cm
Package 2 Length	24 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	240
Package 3 Weight	5.369 kg
Package 3 Height	24.5 cm
Package 3 width	26.5 cm
Package 3 Length	39 cm

Offer Sustainability

EU RoHS Directive	Under investigation
--------------------------	---------------------