



Main

Device short name	MX
Product or component type	Voltage release
Device application	Control
Range compatibility	ComPact NSX EasyPact CVS PowerPact Multistandard ComPact NSX DC
Voltage release type	Shunt trip release
[Uc] control circuit voltage	600 V AC 60 Hz 525 V AC 50 Hz

Complementary

Control signal type	Maintained Impulse
Impulse duration	≥ 20 ms
Threshold tripping voltage	$0.7 \dots 1.1 \times U_n$ opening
Supply inrush power	10 VA
Mounting mode	Fixed
Response time	50 ms
Auxiliary connection terminal	Screw terminal $0 \dots 1.5$ mm ²

Packing Units

Package 1 Weight	0.121 kg
Package 1 Height	0.580 dm
Package 1 width	0.400 dm
Package 1 Length	0.800 dm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------