



### Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Plus
Number of gangs	1 gang
Number of modules	3 modules
Fixing mode	Screws
Colour tint	Ivory
Decoration colour	Ivory

### Complementary

Material	ASA + PC: cover plate ASA + PC: frame-fixing frame
Standards	EN 60669-1
Width	126 mm
Height	90 mm
Depth	30 mm
Product weight	0.095 kg

### Environment

IK degree of protection	IK01
IP degree of protection	IP55
Environmental characteristic	Petrol Liquid soap Bleach UV resistant Oil Window-cleaning fluid

Alcohol  
Acetone

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	92 g
Package 1 Height	3.9 cm
Package 1 width	10.9 cm
Package 1 Length	14.6 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	546 g
Package 2 Height	12.8 cm
Package 2 width	13 cm
Package 2 Length	18.8 cm
Unit Type of Package 3	S03
Number of Units in Package 3	40
Package 3 Weight	4.86 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------