

# Product datasheet

Specifications



## Unica Plus - cover frame (fix. frame) - 1 gang - 4 m - white/white - IP55

MGU11.104.18

### Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Plus
Number of gangs	1 gang
Number of modules	4 modules
Fixing mode	Screws
Colour tint	White
Side color	White

### Complementary

Material	ASA + PC: cover plate ASA + PC: frame-fixing frame
Standards	EN 60669-1
Width	149 mm
Height	90 mm
Depth	30 mm
Net weight	0.107 kg

### Environment

IK degree of protection	IK01
IP degree of protection	IP55
Environmental characteristic	Alcohol Acetone Bleach UV resistant Liquid soap Window-cleaning fluid Petrol Oil

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Weight	108.0 g
Package 1 Height	2.5 cm
Package 1 width	9 cm
Package 1 Length	15 cm
Unit Type of Package 2	P06
Number of Units in Package 2	320
Package 2 Weight	51.324 kg
Package 2 Height	60 cm
Package 2 width	80 cm
Package 2 Length	60 cm
Unit Type of Package 3	S03
Number of Units in Package 3	40
Package 3 Weight	5.336 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------