

# Product datasheet

Specifications



## Unica Basic - cover frame - 1 gang - white/white

MGU2.002.18

### Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Basic
Number of gangs	1 gang
Fixing mode	Clip-in
Cover frame colour tint	White
Decoration colour	White

### Complementary

Material	ASA + PC: decorative frame ASA + PC: cover frame
Standards	EN 60669-1
Height	80 mm
Width	85 mm
Depth	14 mm
Product weight	0.015 kg
Market segment	Residential Small commercial

### Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Window-cleaning fluid UV resistant Oil Bleach Liquid soap Petrol Alcohol Acetone

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Weight	17 g
Package 1 Height	1 cm
Package 1 width	8 cm
Package 1 Length	8.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Weight	406.26 g
Package 2 Height	12.5 cm
Package 2 width	13 cm
Package 2 Length	18.5 cm
Unit Type of Package 3	S03
Number of Units in Package 3	160
Package 3 Weight	3.61 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------