

# Product datasheet

Specifications



## Unica - 1 S.O. - 2P+E, shutters, DE - 2 m - orange

MGU3.037.61

### Main

Range	Unica
Device application	Power supply
Product or component type	Socket-outlet
Aesthetic name	Unica (standard aesthetic)
Device presentation	Mechanism
Socket number	1
Outlet poles configuration	2P + E with shutters
Outlet standard	German
Outlet standard description	Side earth

### Complementary

Rated current	16 A at 250 V AC
Network frequency	50/60 Hz
Number of modules	2 modules
Fixing mode	Clip-in
Colour tint	Orange
Connections - terminals	Screw terminals
Cable cross section	0...4 mm <sup>2</sup> - cable stiffness: flexible 0...4 mm <sup>2</sup> - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 I <sub>n</sub> and 1.1 I <sub>un</sub> , cos phi = 0.6
Electrical durability	10000 cycles, cos phi = 0.8
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Material	ASA + PC: mechanism cover
Surface finish	Brilliant
Quantity per set	Set of 1 blister
Product certifications	FR.ME63.B02375 AC 14.10.01/5433
Embedding depth	30 mm
Depth	40 mm

Width	45 mm
Height	45 mm
Net weight	0.035 kg
Surface treatment	Untreated

## Environment

Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Window-cleaning fluid Acetone Alcohol Bleach Liquid soap Oil UV resistant Petrol

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	36 g
Package 1 Height	4.4 cm
Package 1 width	6.5 cm
Package 1 Length	6.8 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	450 g
Package 2 Height	4.4 cm
Package 2 width	13.6 cm
Package 2 Length	33.5 cm
Unit Type of Package 3	S02
Number of Units in Package 3	40
Package 3 Weight	2.26 kg
Package 3 Height	15 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes

---

<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>
<b>WEEE</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

---

**Contractual warranty**

---

<b>Warranty</b>	18 months
-----------------	-----------

---