

Product datasheet

Specifications



Unica - 1 S.O. - 2P+E, shutters, UK - 2 m - white

MGU3.045.18

Main

Range	Unica
Device application	Power supply
Product or component type	Socket-outlet
Aesthetic name	Unica (standard aesthetic)
Device presentation	Mechanism
Socket number	1
Outlet poles configuration	2P + E with shutters
Outlet standard	British
Outlet standard description	Displaced earth

Complementary

Rated current	13 A at 250 V AC
Network frequency	50/60 Hz
Number of modules	2 modules
Fixing mode	Clip-in
Colour tint	White
Connections - terminals	Screw terminals
Cable cross section	0...4 mm ² - cable stiffness: flexible 0...4 mm ² - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 I _n and 1.1 I _{un} , cos phi = 0.6
Electrical durability	10000 cycles, cos phi = 0.8
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Material	ASA + PC: mechanism cover
Quantity per set	Set of 1 blister
Embedding depth	30 mm
Depth	33 mm
Width	45 mm
Height	45 mm

Product weight	0.0389 kg
----------------	-----------

Environment

Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Oil UV resistant Bleach Petrol Acetone Liquid soap Window-cleaning fluid Alcohol

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	46 g
Package 1 Height	4.4 cm
Package 1 width	6.6 cm
Package 1 Length	6.7 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	460 g
Package 2 Height	4.4 cm
Package 2 width	13.6 cm
Package 2 Length	33.5 cm
Unit Type of Package 3	S02
Number of Units in Package 3	40
Package 3 Weight	2.235 kg
Package 3 Height	15 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure

[Product Environmental Profile](#)

WEEE

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty

18 months
