

# Product datasheet

Specifications



## Unica - rocker switch - 1-way - 10 AX 250 VAC - 1 m - ivory

MGU3.101.25

### Main

Range of product	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	Switch
Device presentation	Mechanism
Technology type	Electromechanical
Switch function	1-pole 1-way
Number of rocker	1
Device application	Light control
Provided equipment	Internal power connection
Colour tint	Ivory

### Complementary

Rated current	10 AX
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Electrical durability	10000 cycles
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	1 module
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm <sup>2</sup> rigid cable 0...2.5 mm <sup>2</sup> flexible cable
Material	ASA + PC: mechanism cover
Fixing mode	Clip-in
Width	22.5 mm

Height	45 mm
Depth	34 mm
Embedding depth	22 mm
Net weight	0.0174 kg
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Standards	EMC directive LV directive EN 60669-1

## Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Bleach Alcohol UV resistant Petrol Oil Acetone Liquid soap Window-cleaning fluid

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	22.0 g
Package 1 Height	4 cm
Package 1 width	6.5 cm
Package 1 Length	6.8 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	274.0 g
Package 2 Height	4.6 cm
Package 2 width	13.6 cm
Package 2 Length	33.6 cm
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Weight	3.775 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>

<b>Toxic heavy metal free</b>	Yes
<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>
<b>WEEE</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------