

Product datasheet

Specifications



Unica - rocker switch - intermediate - 10 AX 250 VAC - 1 m - white

MGU3.105T.18

Main

| | |
|---------------------------|----------------------------|
| Range of product | Unica |
| Aesthetic name | Unica (standard aesthetic) |
| Product or component type | Switch |
| Device presentation | Mechanism |
| Switch function | Intermediate |
| Device application | Control |
| Provided equipment | Internal power connection |
| Colour tint | White |

Complementary

| | |
|---------------------------------------|---|
| Rated current | 10 AX at 250 V AC 50/60 Hz |
| Electrical durability | 10000 cycles |
| Insulation resistance | > 5 MOhm at 500 V |
| Dielectric strength | 2000 V |
| Minimum load breaking capacity | 200 operations 1.25 In and 1.1 Un, cos phi = 0.3 |
| Opening distance | > 3 mm |
| Actuator | Rocker |
| Number of modules | 1 module |
| Connections - terminals | Screw terminals |
| Cable cross section | 0...2.5 mm ² rigid cable 0...2.5 mm ² flexible cable |
| Material | ASA + PC: mechanism cover |
| Fixing mode | Clip-in |
| Width | 22.5 mm |
| Height | 45 mm |
| Depth | 34 mm |
| Embedding depth | 22 mm |
| Net weight | 0.026 kg |
| Ambient air temperature for operation | 25...35 °C |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------------------------|---|
| Ambient air temperature for storage | 0...50 °C |
| Standards | EN 60669-1 EMC directive LV directive |

Environment

| | |
|------------------------------|---|
| IP degree of protection | IP20 |
| IK degree of protection | IK01 |
| Environmental characteristic | Bleach UV resistant Window-cleaning fluid Liquid soap Petrol Acetone Oil Alcohol |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 28 g |
| Package 1 Height | 6.7 cm |
| Package 1 width | 4.4 cm |
| Package 1 Length | 6.8 cm |
| Unit Type of Package 2 | CAR |
| Number of Units in Package 2 | 10 |
| Package 2 Weight | 280 g |
| Package 2 Height | 33.5 cm |
| Package 2 width | 4.4 cm |
| Package 2 Length | 13.6 cm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|