

# Product datasheet

Specifications



## Unica Top/Class - push-button - 1-way - 10 A 250 VAC - 1 m - alu.

MGU3.106T.30

### Main

Range of product	Unica
Aesthetic name	Unica Top - Unica Class
Product or component type	Push-button
Device presentation	Mechanism
Technology type	Electromechanical
Switch function	1-pole 1-way
Number of rocker	1
Device application	Light control
Colour tint	Aluminium

### Complementary

Rated current	10 A
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Electrical durability	40000 cycles, cos phi = 0.6
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Condition of use	Impulse relay control
Opening distance	> 3 mm
Actuator	Push-button
Number of modules	1 module
Connections - terminals	Screw terminals
Cable cross section	0...2.5 mm <sup>2</sup> rigid cable 0...2.5 mm <sup>2</sup> flexible cable
Material	ASA + PC: mechanism cover ABS (acrylonitrile butadiene-styrene): mechanism cover
Fixing mode	Clip-in
Width	22.5 mm

Height	45 mm
Depth	33 mm
Embedding depth	21 mm
Net weight	0.0194 kg
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Standards	EMC directive LV directive EN 60669-1

## Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Oil Acetone UV resistant Petrol Window-cleaning fluid Alcohol Bleach Liquid soap

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	28.0 g
Package 1 Height	6.7 cm
Package 1 width	4.4 cm
Package 1 Length	6.8 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Weight	280.0 g
Package 2 Height	33.5 cm
Package 2 width	4.4 cm
Package 2 Length	13.6 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

---

**WEEE**

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

---

**Contractual warranty**

---

**Warranty**

18 months

---