

# Product datasheet

Specifications



## Unica Top/Class - rocker switch - 10 A, 250 VAC - 1 m - graphite

MGU3.108T.12

### Main

Range	Unica
Device application	Control
Product or component type	Shutter control
Aesthetic name	Unica Top - Unica Class
Device presentation	Mechanism
Rated current	10 A
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Fixing mode	Clip-in
Colour tint	Graphite

### Complementary

Device mounting	Flush
Number of modules	1 module
Technology type	Electromechanical
Actuator	Push-button
Number of rocker	2
Switch function	1-pole 2-way
Switch application	Roller blind
Contacts type and composition	1 C/O
Mechanical interlocking	Interlock between up/down
[Iu] rated interrupted current	2.5 A for motor
Opening distance	> 3 mm
Marking	Down UP
Connections - terminals	Screw terminals
Cable cross section	2.5 mm <sup>2</sup> flexible cable 2.5 mm <sup>2</sup> rigid cable
Minimum load breaking capacity	200 operations 1.25 I <sub>n</sub> and 1.1 U <sub>n</sub> , cos phi = 0.3

<b>Electrical durability</b>	40000 cycles, cos phi = 0.6
<b>Insulation resistance</b>	> 5 MOhm at 500 V
<b>Dielectric strength</b>	2000 V
<b>Material</b>	ASA + PC: mechanism cover
<b>Standards</b>	EMC directive EN 60669-1 LV directive
<b>Ambient air temperature for operation</b>	25...35 °C
<b>Ambient air temperature for storage</b>	0...50 °C
<b>Embedding depth</b>	21 mm
<b>Depth</b>	33 mm

## Environment

<b>IK degree of protection</b>	IK01
<b>IP degree of protection</b>	IP20
<b>Environmental characteristic</b>	Bleach Window-cleaning fluid UV resistant Alcohol Liquid soap Oil Petrol Acetone

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Weight</b>	28.0 g
<b>Package 1 Height</b>	4.4 cm
<b>Package 1 width</b>	6.7 cm
<b>Package 1 Length</b>	6.8 cm
<b>Unit Type of Package 2</b>	BB1
<b>Number of Units in Package 2</b>	10
<b>Package 2 Weight</b>	348.0 g
<b>Package 2 Height</b>	6.8 cm
<b>Package 2 width</b>	12.4 cm
<b>Package 2 Length</b>	18.6 cm
<b>Unit Type of Package 3</b>	P06
<b>Number of Units in Package 3</b>	1280
<b>Package 3 Weight</b>	60.32 kg
<b>Package 3 Height</b>	60 cm
<b>Package 3 width</b>	80 cm
<b>Package 3 Length</b>	60 cm

## Offer Sustainability

<b>Sustainable offer status</b>	Green Premium product
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>EU RoHS Directive</b>	Compliant

---

<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>
<b>WEEE</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

---

### **Contractual warranty**

---

<b>Warranty</b>	18 months
-----------------	-----------

---