

# Product datasheet

Specifications



## Unica - rocker switch - 1-way - 16 AX 250 VAC - 1 m - white

MGU3.161.18

### Main

Range of product	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	Switch
Device presentation	Mechanism
Switch function	1-pole 1-way
Device application	Control
Colour tint	White

### Complementary

Rated current	16 AX at 250 V AC 50/60 Hz
Electrical durability	5000 cycles
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 I <sub>n</sub> and 1.1 U <sub>n</sub> , cos phi = 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	1 module
Connections - terminals	Screw terminals
Cable cross section	0...4 mm <sup>2</sup> rigid cable 0...4 mm <sup>2</sup> flexible cable
Material	ASA + PC: mechanism cover
Fixing mode	Clip-in
Width	22.5 mm
Height	45 mm
Depth	33 mm
Embedding depth	21 mm
Net weight	0.0197 kg
Ambient air temperature for operation	25...35 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Ambient air temperature for storage</b>	0...50 °C
<b>Standards</b>	LV directive EN 60669-1 EMC directive

## Environment

<b>IP degree of protection</b>	IP20
<b>IK degree of protection</b>	IK01
<b>Environmental characteristic</b>	Alcohol Window-cleaning fluid Liquid soap Petrol Acetone Bleach UV resistant Oil

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Weight</b>	22 g
<b>Package 1 Height</b>	4.6 cm
<b>Package 1 width</b>	6.4 cm
<b>Package 1 Length</b>	6.6 cm
<b>Unit Type of Package 2</b>	BB1
<b>Number of Units in Package 2</b>	10
<b>Package 2 Weight</b>	280 g
<b>Package 2 Height</b>	4.4 cm
<b>Package 2 width</b>	13.6 cm
<b>Package 2 Length</b>	33.5 cm
<b>Unit Type of Package 3</b>	S02
<b>Number of Units in Package 3</b>	40
<b>Package 3 Weight</b>	1.5 kg
<b>Package 3 Height</b>	15 cm
<b>Package 3 width</b>	30 cm
<b>Package 3 Length</b>	40 cm

## Offer Sustainability

<b>Sustainable offer status</b>	Green Premium product
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>REACH free of SVHC</b>	Yes
<b>EU RoHS Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>
<b>Toxic heavy metal free</b>	Yes
<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>

---

<b>WEEE</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
-------------	---

---

## **Contractual warranty**

---

<b>Warranty</b>	18 months
-----------------	-----------

---