

Product datasheet

Specifications



Unica - rocker switch - 1-way - 16 AX 250 VAC - 1 m - ivory

MGU3.161.25N

Main

Range of product	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	Switch
Device presentation	Mechanism
Switch function	1-pole 1-way
Device application	Control
Colour tint	Ivory

Complementary

Rated current	16 AX at 250 V AC 50/60 Hz
Electrical durability	5000 cycles
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	1 module
Pilot light	LED, colour: blue, current consumption: 0.15 mA, temperature rise: 15 °C
Connections - terminals	Screw terminals
Cable cross section	0...4 mm ² rigid cable 0...4 mm ² flexible cable
Material	ASA + PC: mechanism cover
Fixing mode	Clip-in
Width	22.5 mm
Height	45 mm
Depth	33 mm
Embedding depth	21 mm
Net weight	0.0239 kg
Ambient air temperature for operation	25...35 °C

Ambient air temperature for storage	0...50 °C
Standards	EMC directive EN 60669-1 LV directive

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Oil Bleach Window-cleaning fluid Alcohol Acetone Liquid soap UV resistant Petrol

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	28 g
Package 1 Height	6.7 cm
Package 1 width	4.4 cm
Package 1 Length	6.8 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Weight	280 g
Package 2 Height	33.5 cm
Package 2 width	4.4 cm
Package 2 Length	13.6 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------