



### Main

Range of product	Unica
Aesthetic name	Unica Top - Unica Class
Product or component type	Switch
Device presentation	Mechanism
Switch function	1-pole 1-way
Device application	Control
Colour tint	Aluminium

### Complementary

Rated current	16 AX at 250 V AC 50/60 Hz
Electrical durability	5000 cycles
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	1 module
Connections - terminals	Screw terminals
Cable cross section	0...4 mm <sup>2</sup> rigid cable 0...4 mm <sup>2</sup> flexible cable
Material	ABS (acrylonitrile butadiene-styrene): mechanism cover
Fixing mode	Clip-in
Width	22.5 mm
Height	45 mm
Depth	33 mm
Embedding depth	21 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Net weight	0.0197 kg
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Standards	EMC directive LV directive EN 60669-1

## Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Window-cleaning fluid UV resistant Bleach Liquid soap Acetone Alcohol Petrol Oil

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	22 g
Package 1 Height	4 cm
Package 1 width	6.6 cm
Package 1 Length	6.6 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	290 g
Package 2 Height	5 cm
Package 2 width	13.6 cm
Package 2 Length	33.6 cm
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Weight	3.97 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

---

Warranty	18 months
----------	-----------

---