

Product datasheet

Specifications



Unica - rocker switch - 2-way - 16 AX 250 VAC - 1 m - white

MGU3.163.18

Main

Range of product	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	Switch
Device presentation	Mechanism
Switch function	1-pole 2-way
Device application	Control
Colour tint	White

Complementary

Rated current	16 AX at 250 V AC 50/60 Hz
Electrical durability	5000 cycles
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	1 module
Connections - terminals	Screw terminals
Cable cross section	0...4 mm ² rigid cable 0...4 mm ² flexible cable
Material	ASA + PC: mechanism cover ABS (acrylonitrile butadiene-styrene): mechanism cover
Fixing mode	Clip-in
Width	22.5 mm
Height	45 mm
Depth	33 mm
Embedding depth	21 mm
Net weight	0.0218 kg
Ambient air temperature for operation	25...35 °C

Ambient air temperature for storage	0...50 °C
Standards	EMC directive LV directive EN 60669-1

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Bleach UV resistant Oil Petrol Acetone Alcohol Liquid soap Window-cleaning fluid

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	26 g
Package 1 Height	4.7 cm
Package 1 width	6.5 cm
Package 1 Length	6.6 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	311 g
Package 2 Height	4.5 cm
Package 2 width	13.5 cm
Package 2 Length	33.5 cm
Unit Type of Package 3	S02
Number of Units in Package 3	40
Package 3 Weight	1.558 kg
Package 3 Height	15 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
-------------	---

Contractual warranty

Warranty	18 months
-----------------	-----------
