



Main

Range of product	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	Switch
Device presentation	Mechanism
Switch function	1-pole 2-way
Device application	Control
Provided equipment	Internal power connection
Colour tint	Ivory

Complementary

Rated current	10 AX at 250 V AC 50/60 Hz
Electrical durability	10000 cycles
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	2 modules
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm ² rigid cable 0...2.5 mm ² flexible cable
Material	ASA + PC: mechanism cover
Fixing mode	Clip-in
Width	45 mm
Height	45 mm
Depth	34 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Embedding depth	22 mm
Product weight	0.0229 kg
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Standards	LV directive EN 60669-1 EMC directive

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Oil Alcohol Petrol Window-cleaning fluid UV resistant Bleach Acetone Liquid soap

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	25.75 g
Package 1 Height	4 cm
Package 1 width	6.5 cm
Package 1 Length	6.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	322 g
Package 2 Height	4.5 cm
Package 2 width	13.5 cm
Package 2 Length	33 cm
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Weight	4.232 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------
