

# Product datasheet

Specifications



## Unica - push-button - 1-way - 10 A 250 VAC - 2 m - white

MGU3.206.18CN

### Main

Range of product	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	Switch
Device presentation	Mechanism
Switch function	1-pole 1-way
Device application	Bell switch
Colour tint	White

### Complementary

Rated current	10 A at 250 V AC 50/60 Hz
Electrical durability	40000 cycles, cos phi = 0.6
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Condition of use	Impulse relay control
Opening distance	> 3 mm
Actuator	Push-button
Number of modules	2 modules
Pilot light	LED, colour: blue, current consumption: 0.15 mA, temperature rise: 15 °C
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm <sup>2</sup> rigid cable 0...2.5 mm <sup>2</sup> flexible cable
Material	ASA + PC: mechanism cover
Marking	Bell symbol
Fixing mode	Clip-in
Width	45 mm
Height	45 mm
Depth	34 mm
Embedding depth	22 mm

Net weight	0.0226 kg
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Standards	LV directive EN 60669-1 EMC directive

## Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	UV resistant Bleach Alcohol Petrol Oil Window-cleaning fluid Acetone Liquid soap

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	26 g
Package 1 Height	4.9 cm
Package 1 width	6.5 cm
Package 1 Length	6.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	332 g
Package 2 Height	4.5 cm
Package 2 width	13.5 cm
Package 2 Length	33.5 cm
Unit Type of Package 3	S02
Number of Units in Package 3	40
Package 3 Weight	1.64 kg
Package 3 Height	15 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>

<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>
<b>WEEE</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
<b>Contractual warranty</b>	
<b>Warranty</b>	18 months