

Product datasheet

Specifications



Unica - push-button - 1-way - 10 A 250 VAC - 2 m - ivory

MGU3.206.25CN

Main

Range of product	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	Switch
Device presentation	Mechanism
Switch function	1-pole 1-way
Device application	Bell switch
Colour tint	Ivory

Complementary

Rated current	10 A at 250 V AC 50/60 Hz
Electrical durability	40000 cycles, cos phi = 0.6
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Condition of use	Impulse relay control
Opening distance	> 3 mm
Actuator	Push-button
Number of modules	2 modules
Pilot light	LED, colour: blue, current consumption: 0.15 mA, temperature rise: 15 °C
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm ² rigid cable 0...2.5 mm ² flexible cable
Material	ASA + PC: mechanism cover
Marking	Bell symbol
Fixing mode	Clip-in
Width	45 mm
Height	45 mm
Depth	34 mm
Embedding depth	22 mm

Net weight	0.0226 kg
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Standards	EN 60669-1 LV directive EMC directive

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Acetone Window-cleaning fluid Liquid soap Bleach Alcohol Petrol UV resistant Oil

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	28 g
Package 1 Height	4 cm
Package 1 width	6.7 cm
Package 1 Length	6.7 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	280 g
Package 2 Height	4.5 cm
Package 2 width	13.5 cm
Package 2 Length	33.4 cm
Unit Type of Package 3	S02
Number of Units in Package 3	40
Package 3 Weight	1.12 kg
Package 3 Height	15 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes

China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Contractual warranty	
Warranty	18 months