

Product datasheet

Specifications



Unica - key card switch - 10 A - 230 VAC - 2 m - white

MGU3.283.18

Main

Range	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	Key card switch
Device application	Control
Device presentation	Mechanism
Cover plate colour tint	White

Complementary

[Ue] rated operational voltage	230 V AC +/- 10 % at 50 Hz
Rated current	10 A
Load type	230 V AC incandescent lamp - 1470 W 230 V AC halogen lamp - 1470 W 230 V AC fan - 1470 W 230 V AC convector - 1470 W Low voltage halogen lamp with ferromagnetic transformer - 1000 VA Low voltage halogen lamp with electronic transformer - 1470 VA Fluorescent tube ferromagnetic ballast - 1470 VA Compact fluorescent lamp - 1470 W LED lamp - 1470 W Contactor
Condition of use	Control through appropriate relay
Actuator	Card 54 x 86 x 0.85 mm (maximum)
Number of modules	2 modules
Fuse type	Electronic
Maximum number of switchings	50000 operations
Pilot light	locator lamp
Marking	Vertical insertion pictogram
Connections - terminals	Soldered connectors
Clamping connection capacity	<= 1 x 2.5 mm ² for flexible cable(s) <= 1 x 2.5 mm ² for rigid cable(s)
Fixing mode	Clip-in
Material	ASA + PC: mechanism cover
Embedding depth	14 mm
Depth	Unica Basic cover frame: 36 mm Unica Colors cover frame: 36 mm Unica Allegro cover frame: 35 mm

Width	45 mm
Height	45 mm

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Ambient air temperature for operation	5...30 °C
Ambient air temperature for storage	-20...60 °C
Environmental characteristic	Bleach Oil Alcohol Acetone Window-cleaning fluid Petrol Liquid soap UV resistant
Standards	EN 61058-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	29 g
Package 1 Height	3.5 cm
Package 1 width	5.9 cm
Package 1 Length	6.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	370 g
Package 2 Height	12.2 cm
Package 2 width	12.7 cm
Package 2 Length	18.5 cm
Unit Type of Package 3	S02
Number of Units in Package 3	40
Package 3 Weight	1.722 kg
Package 3 Height	15 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Contractual warranty	
Warranty	18 months