

Product datasheet

Specifications



Unica Top/Class - 1 RJ45 socket (S-One) - 1 m - Cat.5e, UTP - graph.

MGU3.410.12

Main

| | |
|---------------------------|------------------------------------|
| Range | Unica |
| Aesthetic name | Unica Top - Unica Class |
| Product or component type | RJ45 connector |
| Device application | Communication |
| Device presentation | Mechanism with central plate |
| Colour tint | Graphite |
| Data socket type | RJ45 4 contact(s) Cat.5e < 155 MHz |
| Provided equipment | Protective flap Label holder |

Complementary

| | |
|-----------------------------|--|
| Communication network type | 1000BASE-T |
| Communication port protocol | ATM 155 Mbps |
| Product destination | Duct Floor box |
| Number of modules | 1 module |
| Socket number | 1 |
| Type of footprint | Infraplus |
| Connector type | S-One |
| Cable shielding type | U/UTP |
| Organization of wire | Unshielded twisted pair |
| Connections - terminals | Click |
| Device mounting | Flush |
| Fixing mode | Clip-in By clips: shield |
| Installation direction | Straight |
| Material | ABS (acrylonitrile butadiene-styrene): mechanism cover |
| Depth | 36 mm |
| Width | 22.5 mm |
| Height | 45 mm |
| Embedding depth | 25 mm |

Environment

| | |
|---------------------------------------|---|
| IP degree of protection | IP40 |
| IK degree of protection | IK01 |
| Ambient air temperature for operation | 15...30 °C |
| Ambient air temperature for storage | 0...35 °C |
| Environmental characteristic | Bleach Petrol Alcohol Oil Liquid soap Window-cleaning fluid Acetone UV resistant |
| Standards | ISO 8877 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 19.3 g |
| Package 1 Height | 2.5 cm |
| Package 1 width | 3.8 cm |
| Package 1 Length | 4.5 cm |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Weight | 254.8 g |
| Package 2 Height | 5.5 cm |
| Package 2 width | 11 cm |
| Package 2 Length | 24.6 cm |
| Unit Type of Package 3 | S03 |
| Number of Units in Package 3 | 170 |
| Package 3 Weight | 4.752 kg |
| Package 3 Height | 30 cm |
| Package 3 width | 30 cm |
| Package 3 Length | 40 cm |

Offer Sustainability

| | |
|----------------------------|---|
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

Warranty

18 months