

Product datasheet

Specifications



Unica - 1 RJ45 socket (S-One) - 1 m - Cat.6, S/FTP - white

MGU3.416.18

Main

Range	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	RJ45 connector
Device application	Communication
Device presentation	Mechanism with central plate
Colour tint	White (RAL 9003)
Data socket type	RJ45 4 contact(s) Cat.6 < 250 MHz
Provided equipment	Protective flap Label holder

Complementary

Communication network type	1000BASE-TX
Communication port protocol	ATM 1200 Mbps
Product destination	Floor box Duct
Number of modules	1 module
Socket number	1
Type of footprint	Infraplus
Connector type	S-One
Cable shielding type	S/FTP
Organization of wire	Shielded twisted pair
Connections - terminals	Click
Device mounting	Flush
Fixing mode	Clip-in By clips: shield
Installation direction	Straight
Material	ASA + PC: mechanism cover
Depth	36 mm
Width	22.5 mm
Height	45 mm
Embedding depth	25 mm

Environment

IP degree of protection	IP40
IK degree of protection	IK01
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
Environmental characteristic	Window-cleaning fluid Bleach Oil Liquid soap Alcohol UV resistant Petrol Acetone
Standards	ISO 8877

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	44 g
Package 1 Height	4.6 cm
Package 1 width	7.3 cm
Package 1 Length	7.3 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	484 g
Package 2 Height	5.6 cm
Package 2 width	11 cm
Package 2 Length	24.7 cm
Unit Type of Package 3	S03
Number of Units in Package 3	170
Package 3 Weight	8.7 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------