



### Main

Range	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	RJ45 connector
Device application	Communication
Device presentation	Mechanism with central plate
Colour tint	Ivory
Data socket type	RJ45 4 contact(s) Cat.6 < 250 MHz
Provided equipment	Label holder Protective flap

### Complementary

Communication network type	1000BASE-TX
Communication port protocol	ATM 1200 Mbps
Product destination	Duct Floor box
Number of modules	2 modules
Socket number	1
Type of footprint	Infraplus
Connector type	S-One
Cable shielding type	S/FTP
Organization of wire	Shielded twisted pair
Connections - terminals	Click
Device mounting	Flush
Fixing mode	Clip-in By clips: shield
Installation direction	Straight
Material	ASA + PC: mechanism cover
Depth	36 mm
Width	85 mm
Height	80 mm
Embedding depth	25 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

IP degree of protection	IP40
IK degree of protection	IK01
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
Environmental characteristic	Window-cleaning fluid Liquid soap Acetone UV resistant Petrol Oil Alcohol Bleach
Standards	ISO 8877

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	41 g
Package 1 Height	6 cm
Package 1 width	10 cm
Package 1 Length	7.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	494 g
Package 2 Height	8.2 cm
Package 2 width	17.7 cm
Package 2 Length	18.5 cm
Unit Type of Package 3	S02
Number of Units in Package 3	20
Package 3 Weight	1.44 kg
Package 3 Height	15 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------