



Main

Aesthetic name	Unica (standard aesthetic)
Product or component type	Rotary dimmer
Device presentation	Mechanism
Fixing mode	Clip-in
Dimmer application	Resistive load Inductive load
[Ue] rated operational voltage	230 V AC 50 Hz
Number of modules	2 modules
Cover plate colour tint	White

Complementary

Dimmer control	270° rotary setting ON/OFF push
Maximum permanent current	1.74 A
Total number of wires	2
Load type	230 V AC halogen lamp - 40...400 W 230 V AC incandescent lamp - 40...400 W Low voltage halogen lamp with ferromagnetic transformer - 40...400 VA
Protection type	Fuse protection
Fuse type	4 Ah 5 x 20 mm 230 V 50 Hz
Marking	L+N
Connections - terminals	Screw terminals
Clamping connection capacity	<= 2 x 2.5 mm ²
Connected auxiliaries	2-way switch
Material	ASA + PC: mechanism cover
Standards	EN 60669-2-1
Product certifications	CE
Ambient air temperature for operation	5...30 °C
Ambient air temperature for storage	-20...60 °C
Embedding depth	34 mm
Depth	54 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	45 mm
Height	45 mm
Net weight	0.071 kg

Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Acetone Liquid soap Petrol UV resistant Oil Alcohol Bleach Window-cleaning fluid

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	121 g
Package 1 Height	6.4 cm
Package 1 width	9.8 cm
Package 1 Length	10.8 cm

Offer Sustainability

EU RoHS Directive	Under investigation
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------