

Product datasheet

Specifications



Unica Top/Class - buzzer - 230V AC - 2 m - clip-in - graphite

MGU3.785.12

Main

Range	Unica
Device application	Signalling
Product or component type	Buzzer
Aesthetic name	Unica Top - Unica Class
Device presentation	Mechanism
[Ue] rated operational voltage	230 V AC 50/60 Hz
Number of modules	2 modules
Fixing mode	Clip-in
Colour tint	Graphite

Complementary

Current consumption	40 mA
Type of setting	Volume can be adjusted using a screw
Device mounting	Flush
Operating time	0...60 ms
Connections - terminals	Screw terminals
Acoustic level	Between 76 and 80 dB
Cable cross section	0.75...1.5 mm ² flexible cable 0.75...1.5 mm ² rigid cable
Material	ASA + PC: mechanism cover
Standards	LV directive EMC directive CE
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
Embedding depth	31 mm
Depth	42 mm
Width	45 mm
Height	45 mm
Net weight	0.048 kg

Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Petrol Acetone UV resistant Liquid soap Bleach Alcohol Oil Window-cleaning fluid

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	40.0 g
Package 1 Height	4.2 cm
Package 1 width	4.5 cm
Package 1 Length	4.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	504.0 g
Package 2 Height	13 cm
Package 2 width	12.5 cm
Package 2 Length	18.7 cm
Unit Type of Package 3	S02
Number of Units in Package 3	40
Package 3 Weight	2.294 kg
Package 3 Height	15 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------